

T39 Serie Lötspitzen

Unit: mm

Shape B

| | | | | |
|-----------------|-----------------|----------------|-----------------|------------------|
| T39-B02 | T39-B05 | T39-B07 | T39-BL02 | T39-BLL02 |
| | | | | |
| T39-BS02 | T39-BS03 | | | |
| | | | | |

Shape BC

| | | | | |
|-------------------|---------------------|---------------------|---------------------|-------------------|
| T39-BC1020 | T39-BC1530 | T39-BC2040 | T39-BC2535 | T39-BC3065 |
| | | | | |
| T39-BC3545 | T39-BCF1020* | T39-BCF2535* | T39-BCF3545* | |
| | | | | |

Shape BCM

| | |
|--------------------|--------------------|
| T39-BCM2535 | T39-BCM3545 |
| | |

Shape C


| | | | |
|------------------|------------------|------------------|--------------------|
| T39-C1020 | T39-C1025 | T39-C4055 | T39-CF4055* |
| | | | |

Shape D



| | | | | |
|------------------|-----------------|-----------------|----------------|-----------------|
| T39-D08 | T39-D12 | T39-D16 | T39-D24 | T39-D32 |
| | | | | |
| T39-D4 | T39-D52 | T39-DL32 | T39-DL4 | T39-DL52 |
| | | | | |
| T39-DLS15 | T39-DS24 | T39-DS32 | T39-DS4 | T39-DS52 |
| | | | | |

* Vorverzinkt nur auf der Schnittfläche


Shape I




Shape J















Shape K




with slot




with V-groove



Spatula



Der FX-9702 Stickstoff-LötKolben kann mit Lötspitzen mit der N₂ Markierung verwendet werden. Verwenden Sie eine Spitze mit einer geeigneten Düse.



| | | | |
|---------|---------|---------|---------|
| A B5290 | B B5291 | C B5292 | D B5293 |
| E B5294 | F B5295 | G B5296 | H B5297 |
| I B5298 | J B5332 | K B5333 | |



Setup with N₂ system